

[See all 65 Products in Family](#)

# Basler ace2 a2A5328-15umPRO Monochrome USB3 Pro Camera

See More by [Basler](#)



Basler ace2 USB 3.0 Cameras (Front)



Stock **#16-639** [CONTACT US](#)

[Similar Cameras](#)

- 1 + MRP ₹3,09,042

**1** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹3,09,042 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome

Spectrum:

### General

Monochrome Camera

Type:

a2A5328-15umPRO

Model Number:

Basler  
ace2

**Manufacturer:**  
**Camera Series:**

## Physical & Mechanical Properties

36.3 x 29 x 29 (excludes connectors and lens mount)

**Dimensions (mm):**

<90

**Weight (g):**

Full

**Housing:**

## Sensor

Not Specified

**Image Buffer:**

1.2"

**Sensor Format:**

24.40

**Resolution (Megapixels):**

15.00

**Frame Rate (fps):**

5,330 x 4,608

**Pixels (H x V):**

2.74 x 2.74

**Pixel Size, H x V (µm):**

14.6 x 12.6

**Sensing Area, H x V (mm):**

Sony IMX540

**Imaging Sensor:**

Progressive Scan CMOS

**Type of Sensor:**

Global

**Shutter Type:**

8/10/12 Bit

**Pixel Depth:**

Freely Programmable

**Exposure Time:**

70.8

**Dynamic Range (dB):**

USB3 Vision v1.0, GenICam

**Machine Vision Standard:**

## Electrical

3.8

**Power Consumption (W):**

## Hardware & Interface Connectivity

USB 3.0

**Interface:**

USB 3.0, Micro-B

**Connector:**

Power over USB

**Power Supply:**

1 opto-coupled input line, 2 general purpose I/O (GPIO) lines

**GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or Free-Run

**Synchronization:**

Back Panel

**Interface Port Orientation:**

6-pin M8

**GPIO Connector Type:**

## Threading & Mounting

C-Mount

**Mount:**

1/4-20 with Tripod Mount Adapter [#16-641](#)

**Mounting Threads:**

## Environmental & Durability Factors

-10 to +60

**Operating Temperature (°C):**

-20 to +80

**Storage Temperature (°C):**

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:

Compliant

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- USB 3.0 with SONY Pregius S Sensors up to 24MP and 160 fps
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace USB 3.0 Cameras](#) Also Available

Basler ace2 USB 3.0 Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust MB connector. The Basler ace2 USB 3.0 Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (USB3 Vision) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both USB 3.0 and GigE interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.


## Technical Information



IMX676 Sensor QE Curve



IMX900 Sensor QE Curve



GMAX2505 Sensor QE Curve



IMX546 Sensor QE Curve



IMX545 Sensor QE Curve



GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve

;