

BBO Crystal, 30um Thick, 12fs - 10ps



Stock #72-887 **1 In Stock**

1 MRP ₹1,62,486

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-2	₹1,62,486 each
Qty 3+	₹1,46,025 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Thickness (µm):

Regulatory Compliance

Certificate of Conformance:[View](#)**Country of Origin:**

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Compatible with Ultrafast Pulses Ranging from 12fs to 20ps
- User Swappable SHG Crystal with No Realignment Required
- VideoFROGScan Software Provides Real-Time Measurements

Mesa Photonics FROGScan Ultrafast Pulse Measurement System combines high accuracy, high dynamic range, and real-time pulse measurement in an easy-to-use package, making it ideal for ultrafast pulse characterization, dispersion compensation calculation, and pulse distortion diagnosis. By swapping the internal SHG crystal, the user can tune the system to meet their application needs across 12fs to 20ps pulse widths. The crystal is kinematically mounted in the system and the included VideoFROGScan control software reads the crystal specifications to remove the need for realignment after swapping. Mesa Photonics FROGScan Ultrafast Pulse Measurement System is designed to integrate seamlessly into existing experimental setups with a small 33cm x 22cm x 22cm footprint, USB interface, and an easy to align optical platform. The system's high speed, 16-bit data acquisition system ensures minimal distortion at high pulse repetition rates.