

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [FLIR Blackfly® PoE GigE Cameras](#)

[See all 22 Products in Family](#)

BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Color Camera

See More by [FLIR](#)



FLIR Blackfly® PoE GigE Cameras (Front)



Stock **#34-510** 10 TO 12 DAYS

[Similar Cameras](#)



1



₹50,808.00

ADD TO CART

Qty 1+

₹50,808.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: FLIR
Mounting Threads: ¼-20 with Tripod Mount Adapter #88-210
Image Buffer: 16MB
Camera Family: Blackfly®
Model Number: BFLY-PGE-31S4C-C
Imaging Sensor: Sony IMX265
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 3.20
Pixels (H x V): 2,048 x 1,536
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 7.07 x 5.3
Frame Rate (fps): 35.00
Pixel Depth: 8/12/16/24 bit
Exposure Time: 18µs - 11.9s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately: USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: #88-063
Power Consumption (W): 2.5
GPIOs: 1 opto-isolated input, 1 opto-isolated output
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 30 (excludes connectors and lens mount)
Weight (g): 36
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.80
Operating Temperature (°C): 0 to +45
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

