

BFS-U3-200S6M-C USB 3.1 Blackfly® S, Monochrome Camera

See More by [FLIR](#)



FLIR Blackfly® S USB3 Camera (front)



Stock **#11-521** 10 TO 12 DAYS

[Similar Cameras](#)



1



₹60,813.00

ADD TO CART

Qty 1+

₹60,813.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:
Monochrome Camera

Manufacturer: FLIR
Mounting Threads: ¼-20 with Tripod Mount Adapter #88-210
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-U3-200S6M-C
Imaging Sensor: Sony IMX183
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1"
Resolution (MegaPixels): 20.00
Pixels (H x V): 5,472 x 3,648
Pixel Size, H x V (µm): 2.4 x 2.4
Sensing Area, H x V (mm): 13.13 x 8.76
Frame Rate (fps): 18.00
Pixel Depth: 10/12 bit
Exposure Time: 67µs - 30s
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB or via GPIO with #88-063
Power Consumption (W): <3
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 30 (excludes connectors and lens mount)
Weight (g): 36
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.89
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

