

[See all 10 Products in Family](#)

Blue 200 x 200 Flat Dome Light



Effilux Flat Dome Lights

Stock **#22-107** [CONTACT US](#)

1 MRP ₹88,449

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹88,449 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Model Number:
EFFI-FD-200-200-465

Type of Illumination:
LED Illuminator

Manufacturer:
Effilux

Geometry:
Flat Dome Light

Constant **Illumination Mode:**

Physical & Mechanical Properties

239 x239 x43.2 **Dimensions (mm):**

1900 **Weight (g):**

200 x200 **Active Area (mm):**

Optical Properties

Blue **Color:**

465 **Wavelength (nm):**

Electrical

30 **Power Consumption (W):**

Hardware & Interface Connectivity

24 **Input Voltage (V):**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#15-874](#)
Europe: [#15-875](#)
Japan: [#73-409](#)
Korea: [#73-409](#)
China: [#15-874](#)

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

France **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Effilux Flat Dome Lights achieve diffuse illumination similar to standard dome lights but with a thinner, more compact housing. These flat dome lights provide a large imaging area for increased depth of focus and field of view. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Effilux Flat Dome Lights offer greater than 90% uniformity and feature an anti-reflection system that absorbs unwanted light. Flat Dome Lights are ideal for imaging textured, shiny, or uneven surfaces.