

[See all 10 Products in Family](#)

Blue 200 x 200 Flat Dome Light



Effilux Flat Dome Lights

Stock **#22-107** [CONTACT US](#)

-

1

+

₹74,430

ADD TO CART

Volume Pricing	
Qty 1+	₹74,430 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
EFFI-FD-200-200-465	Model Number:
LED Illuminator	Type of Illumination:
Effilux	Manufacturer:
Flat Dome Light	Geometry:

Constant	Illumination Mode:
Physical & Mechanical Properties	
239 x239 x43.2	Dimensions (mm):
1900	Weight (g):
200 x200	Active Area (mm):
Optical Properties	
Blue	Color:
465	Wavelength (nm):
Electrical	
30	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately: USA: #15-874 Europe: #15-875 Japan: #73-409 Korea: #73-409 China: #15-874	
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
France	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Efflux Flat Dome Lights achieve diffuse illumination similar to standard dome lights but with a thinner, more compact housing. These flat dome lights provide a large imaging area for increased depth of focus and field of view. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Efflux Flat Dome Lights offer greater than 90% uniformity and feature an anti-reflection system that absorbs unwanted light. Flat Dome Lights are ideal for imaging textured, shiny, or uneven surfaces.