

Blue M34 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-707 10 TO 12 DAYS

1

₹12,615.00

ADD TO CART

Qty 1-9
₹12,615.00
Qty 10+
₹12,032.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1218

Clear Aperture CA (mm):
29.00

Coating:
Hard Coated

Filter Thread:

M34 x 0.50
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 36.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View