

TECHSPEC[®] C-Mount Female Aperture Cap



C-Mount Female Aperture Cap

Stock #55-245 5 In Stock

-

1

+

₹2,109

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,109 each
Qty 5-9	₹1,885 each
Qty 10-25	₹1,768 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Function:

Tube Cap

Physical & Mechanical Properties

Total Length (mm):	
3.0	
Thickness (mm):	
3.00	
Threading & Mounting	
Thread Type:	
C-Mbunt	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

PRODUCT DETAILS

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mbunt components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mbunt Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** #11-139 and #11-142 each include one S-Mbunt Aperture Cap (#11-137)

TECHNICAL INFORMATION

