

[See all 14 Products in Family](#)

Cable length 10m M16 12-pin plug (female), flying leads



LUMMAX® SWIR Area Lights

Stock **#90-882** NEW **3 In Stock**

-

1

+

MRP ₹12,833

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹12,833 each
Need More?	Request Quote

Product Downloads

General	
115.0000.05	Model Number:
Note: Compatible with LUMMAX® SWIR Area Lights (PID) & Configurable Ring Lights (PID)	

LUMMAX®	Manufacturer:
---------	---------------

Physical & Mechanical Properties	
	Length (m):

10	
610	Weight (g):
Hardware & Interface Connectivity	
M16 12-pin plug (female) & flying leads	Connector:
19 - 30 VDC	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- SWIR Wavelengths Options from 980 – 1600nm
- Compact 40 x 40mm Form Factor
- IP64 Rated for Dust and Moisture Protection

LUMIMAX® SWIR Area Lights provide powerful short-wave infrared (SWIR) illumination for demanding machine vision and inspection applications. Designed for wavelengths ranging from 980nm to 1600nm, these compact 40 x 40mm LED area lights deliver uniform, high-intensity output optimized for material sorting, semiconductor inspection, and moisture detection. An optional LUMIMAX Control Box (#90-883) simplifies power management and brightness adjustment, ensuring stable and consistent illumination performance. LUMIMAX® SWIR Area Lights feature industrial-grade construction, versatile mounting options, and are can be used as spot, area, or backlight illuminators. These lights are ideal for applications requiring enhanced material contrast beyond the visible spectrum, and they provide reliable illumination for automation, quality control, and research environments.