

Cyan M25.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-742 10 TO 12 DAYS

-

1

+

₹10,788.00

ADD TO CART

Qty 1-9
₹10,788.00
Qty 10+
₹10,240.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-450, 600-1020

Clear Aperture CA (mm):
21.00

Coating:
Hard Coated

Filter Thread:

M25.5 x 0.50
Color: Cyan
Center Wavelength CWL (nm): 505.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 90.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 27.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View