

Cyan M46 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-640** 10 TO 12 DAYS

⊖ 1 ⊕

₹16,182.00

ADD TO CART

Qty 1-9
₹16,182.00
Qty 10+
₹15,242.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-450, 600-1014

Clear Aperture CA (mm):
41.00

Coating:
Hard Coated

Filter Thread:

M46 x 0.75
Color: Cyan
Center Wavelength CWL (nm): 505.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 90.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 48.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View