

Cyan M58 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-725 10 TO 12 DAYS

- 1 + ₹18,792.00

ADD TO CART

Qty 1-9
₹18,792.00
Qty 10+
₹17,922.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm): 200-450, 600-1019
Clear Aperture CA (mm): 53.00
Coating: Hard Coated
Filter Thread:

M58 x 0.75
Color: Cyan
Center Wavelength CWL (nm): 505.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 90.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 60.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View