

Preloaded Norland Optical Adhesive NOA 65 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#55-087** 10 TO 12 DAYS

- 1 + **₹2,828.00**

ADD TO CART

Qty 1-4
₹2,828.00
Qty 5+
₹2,732.00
Volume Pricing
Request Quote

Get Product Downloads
Size (oz): 0.34
Size (cc): 10.00
Glass Bonding: Good

Metal Bonding: Good
Plastic Bonding: Fair
Viscosity (cps): 1200
Durability: Flexible
Index of Refraction n_d: 1.52 @ 589nm
Norland Number: 65
Shelf Life: 6 months
Type: Barrel
Typical Applications: More flexible adhesive for extra low strain applications. Suitable for cold blocking applications.
Note: Contains 10g of adhesive
Absorption Range (nm): 350 - 380
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 4.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant