

# Preloaded Norland Optical Adhesive NOA 88 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#14-840** 10 TO 12 DAYS

- 1 + **₹3,306.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| ₹3,306.00                     |
| Qty 5+                        |
| ₹3,106.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

|                                    |
|------------------------------------|
| <b>Size (oz):</b><br>0.34          |
| <b>Glass Bonding:</b><br>Excellent |
| <b>Metal Bonding:</b><br>Excellent |

|                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------|
| <b>Plastic Bonding:</b><br>Fair                                                                                                |
| <b>Viscosity (cps):</b><br>250                                                                                                 |
| <b>Durability:</b><br>Hard & Flexible                                                                                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.56 @ 589nm                                                                   |
| <b>Norland Number:</b><br>88                                                                                                   |
| <b>Shelf Life:</b><br>4 months                                                                                                 |
| <b>Type:</b><br>Barrel                                                                                                         |
| <b>Typical Applications:</b><br>Low outgassing and low viscosity for bonding glass or metal. Excellent transmission in the UV. |
| <b>Note:</b><br>Contains 10g of adhesive                                                                                       |
| <b>Absorption Range (nm):</b><br>315 - 395                                                                                     |
| <b>Bonding Type:</b><br>Glass to Glass/Metal                                                                                   |
| <b>Energy for Full Cure (J/cm<sup>2</sup>):</b><br>5                                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |