

[See all 4 Products in Family](#)

Dual Axis Linear Scale Micrometer



Stock **#58-608** [CONTACT US](#)

- 1 + MRP ₹70,623

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹70,623 each
Qty 5+	₹67,150 each
Need More?	Request Quote

Product Downloads

General

No **NIST Certification:**

Physical & Mechanical Properties

Metric: 25µm
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

Thickness (mm):
1.50 ±0.100

Dimensional Tolerance (mm):
±0.100

Optical Properties

Chrome on Glass **Substrate:** □

60-40 **Surface Quality:**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

