

[See all 4 Products in Family](#)

## Dual Axis Linear Scale Micrometer



Stock **#58-608** **1 In Stock**

₹52,200

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹52,200 each
Qty 5+	₹49,626 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

**NIST Certification:**  
No

#### Physical & Mechanical Properties

**Scale Divisions:**  
Metric: 25µm  
English: 1 mil (0.001")

**Dimensions (mm):**  
25.4 x 76.2

**Thickness (mm):**

1.50 ±0.100

**Dimensional Tolerance (mm):**

±0.100

## Optical Properties

**Substrate:**

Chrome on Glass

**Surface Quality:**

60-40

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 235:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited

## Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

## Technical Information

