

English Plate for 2.62" Stages, Top Plate 1/4-20



Stock #55-651 **20+ In Stock**

- 1 + ₹2,347

ADD TO CART

Volume Pricing

Qty 1+	₹2,347 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Compatible with 2.62" Stages **Note:**

Physical & Mechanical Properties

0.375 **Thickness (inches):**

1/4-20 **Center Hole:**

Dimensions (inches):

2.62 x 2.62

S.H.C.S. C'bore:

(4) #10 on 1.414" Sq. (2.00" B.C.)

Regulatory Compliance

RoHS 2015:
Compliant

Reach 224:
Compliant

Certificate of Conformance:
View

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited

Product Details

- Mounts English/Metric Post or Post Holders to Translation Stages
- Center 1/4-20, M6 x 1.0 or M16 x 1.0 Threaded Hole
- Black Anodized Aluminum Construction

These adapter plates permit the mounting of standard English 1/4-20 or Metric M6 x 1.0 and M16 x 1.0 components to the top of our [translation stages](#) and [ball bearing slides](#). Use dimension "A" below to match the width of the top plate with the width of the ball bearing slide or translation stage (not all slides conform to this). Counterbore "E" and spacing "B" must also match the top mounting holes and spacing of the stage or slide. M16 hole is not available for 1.25" top plates. Please see diagram below for more details. All dimensions are in inches.

Technical Information

A	B	C	D	Mounting Hole E	Mounting Hole F	Thickness	Stock No.
1.25"	0.75"	0.25"	0.625"	#4	1/4-20	0.25"	#55-646
					M6 x 1.0	6.35mm	#55-647
1.75"	1.00"	0.375"	0.875"	#6	1/4-20	0.25"	#55-648
					M6 x 1.0	6.35mm	#55-649
					M16 x 1.0	6.35mm	#55-650
2.62"	1.414"	0.603"	1.31"	#10	1/4-20	0.375"	#55-651
					M6 x 1.0	9.525mm	#55-652
					M16 x 1.0	9.525mm	#55-653

