

Fiber Optic Cutting Block



Stock #54-013 **10 In Stock**

- 1 + MRP ₹4,885

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹4,885 each
Qty 5+	₹4,328 each
Need More?	Request Quote

Product Downloads

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,

Product Details

- Cleaves Jacketed and Unjacketed Fiber
- Accepts Fiber up to 3300µm Diameter
- Blade Included

Fiber Optic Cutting Blocks use tight tolerance guide holes to position fibers for cutting with standard blades (included). Jacketed and unjacketed fibers may be cleaved with this instrument: from 750 to 3000 micron unjacketed, 750 to 1500 micron jacketed (includes duplex fibers), and all 265 micron fiber bundles. Holes accept 750 to 3300 micron outer diameters. The Fiber Optic Cutting Block features a $90^{\circ} \pm 0.2^{\circ}$ cutting angle. Cutting block included with Optical Fiber Hot Knife [#54-014](#).
