

# Fiber Optic Taper For 18mm to 11mm



Stock #55-135 10 TO 12 DAYS

- 1 +

₹101,007.00

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| ₹101,007.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Diameter Tolerance (mm):  
±0.5, Large End

Distortion (%):  
3.00

Substrate: ☐  
[Schott 24 Glass with EMA](#)

Height (mm):  
15.25

Diameter of Large End (mm):  
20.00

|                                                                          |
|--------------------------------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>1.00                                    |
| <b>Operating Temperature (°C):</b><br>-10 to +300                        |
| <b>Resolution:</b><br>102 lp/mm                                          |
| <b>Size Ratio:</b><br>18:11 mm                                           |
| <b>Size of Small End (mm):</b><br>12.50                                  |
| <b>Surface Quality:</b><br>30-20                                         |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                 |
| <b>Resolving Power (µm):</b><br>6.00                                     |
| <b>Dimensional Tolerance (mm):</b><br>±0.1                               |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>6.8 |
| <b>Core/ Clad Ratio:</b><br>70 / 30                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |