

Fiber Optic Taper For 18mm to 8mm



Stock #55-134 10 TO 12 DAYS

-

1

+

₹85,434.00

ADD TO CART

Qty 1+
₹85,434.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter Tolerance (mm):
±0.5, Large End

Distortion (%):
3.00

Substrate: [Schott 24 Glass with EMA](#)

Height (mm):
15.25

Diameter of Large End (mm):
20.00

Numerical Aperture NA: 1.00
Operating Temperature (°C): -10 to +300
Resolution: 102 lp/mm
Size Ratio: 18:8 mm
Size of Small End (mm): 8.80
Surface Quality: 30-20
Thickness Tolerance (mm): ±0.1
Resolving Power (µm): 6.00
Dimensional Tolerance (mm): ±0.1
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.8
Core/ Clad Ratio: 70 / 30

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View