

1/2" x 36", Flexible Fiber Optic Light Guide



1/2" Flexible Fiber Optic Light Guide

Stock #39-370 10 TO 12 DAYS

-

1

+

₹33,930.00

ADD TO CART

Qty 1+
₹33,930.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Acceptance Angle (°):
68.00

Minimum Bend Radius (mm):
50.8

Diameter (inches):
0.50

Length (inches):
36.00

Numerical Aperture NA: 0.55
Operating Temperature (°C): -40 to +107
Fiber Diameter (µm): 50.00
Packing Fraction (%): 82% nominal
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-946 MX: #66-908
Geometry: Spot Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View
