

[See all 8 Products in Family](#)

3/4" Dia Stainless Posts, Vertical Post 24"



Stock **#52-100** **5 In Stock**

-

1

+

₹9,022

ADD TO CART

Volume Pricing	
Qty 1+	₹9,022 each
Need More?	Request Quote

Product Downloads

General

Mounting Post	Type:
---------------	-------

Physical & Mechanical Properties

609.6	Length (mm):
2.25	Weight (lbs):
24.0	Length (inches):
	Diameter (inches):

Threading & Mounting

3/4-16 Male (One End)

Mounting Threads:

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

View

Certificate of Conformance:

United States

Country of Origin:

Edmund Optics India Private Limited

Imported By:

Product Details

- Posts for Integration into Imaging Systems
 - Vertical Posts Thread to Bases and Platforms
 - Horizontal Arms Thread to Posts and Microscope Head Mounts
 - [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available
- Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are ¾ of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with ¾"-16 male or threaded on both ends with a combination of ¼"-20 and 5/16"-18 pins.