

Glan-Taylor Polarizer 350 - 2300nm, 8mm



Glan-Taylor Polarizer

Stock **#89-547** [CONTACT US](#)



1



₹74,385.00

ADD TO CART

Qty 1-5
₹74,385.00
Qty 6+
₹70,905.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
8.0

Coating:
Single Layer MgF₂

Diameter (mm):
25.40

Extinction Ratio:

<5 x 10 ⁻⁵
Substrate: Calcite
Length (mm): 17.00
Surface Quality: 20-10
Type: Linear Polarizer
Construction: Crystalline Glan-Taylor Polarizer
Transmitted Wavefront, P-V: λ/2 @ 632.8nm
Beam Deviation (arcmin): <3
Transmitted Wavefront Distortion (RMS): λ/4 @ 632.8 nm
Wavelength Range (nm): 350 - 2300
Damage Threshold, By Design: 2 J/cm² @ 1064nm, 10ns, 10Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant