

Glan-Thompson Polarizer Adapter



#58-479

Glan-Thompson Polarizer Adapter, #58-479

Stock #58-479 **4 In Stock**

⊖ 1 ⊕ MRP ₹14,932

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹14,932 each |
| Qty 5-25 | ₹14,205 each |
| Qty 26-49 | ₹12,712 each |
| Need More? | Request Quote |

Product Downloads

General

Mounting Type: Polarizing Prism Holder

Note:

Threading & Mounting

Mounting Tube Outer Diameter (mm):

34.0

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

Japan Country of Origin:

Imported By:
 Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- Coarse and Fine Movement Available
- Black Anodized Aluminum
- [Posts](#) and [Post Holders](#) Required for Mounting

Metric Polarizer Mounts feature secure optic retainer, lever arm for smooth rotation, locking knob for repeatability and 360° scaled vernier. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard. Micrometer version provides fine adjustment. Metric Polarizer Mounts, for Micrometer Driven version only: total travel of the 0.25mm pitch fine adjustment screw is 10°. Total angular rotation per rotation of knob is 20 minutes. *40mm total including 34mm diameter mounting tube.

Technical Information

| Diameter of Compatible Optics D | Clear Aperture CA | Drive Type | Mount Diameter A | Mount Thickness B | C | E | Stock No. |
|---------------------------------|-------------------|------------|------------------|-------------------|----|------|-------------------------|
| Standard | | | | | | | |
| 20.0 | 17 | Standard | 50 | 19 | 34 | 24.0 | #55-454 |
| 25.4 | 22 | Micrometer | 69 | - | - | 33.5 | #55-011 |
| 25.4 | 22 | Standard | 60 | 20 | 42 | 29.5 | #55-010 |
| 30.0 | 27 | Micrometer | 69 | - | - | 33.5 | #57-570 |
| 30.0 | 27 | Standard | 60 | 20 | 42 | 29.5 | #57-569 |
| 50.0 | 47 | Micrometer | 89 | - | - | 43.5 | #56-329 |
| 50.0 | 47 | Standard | 80 | 20 | 62 | 39.5 | #55-455 |
| Glan-Thompson Polarizer Mounts | | | | | | | |
| 25.4 | 18 | Micrometer | 69 | -* | - | 33.5 | #57-572 |
| 25.4 | 18 | Standard | 60 | 20* | 42 | 29.5 | #57-571 |



