

[See all 22 Products in Family](#)

Green, 2" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#91-061** NEW **1 In Stock**

-

1

+

₹1,00,607

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,00,607 each
Need More?	Request Quote

Product Downloads

General	
DL225-050530IC	Model Number:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Diffuse Axial	Geometry:

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):

128 L x 60 W x 57 T

Weight (g):

351.9

Aperture Size:

~2" x 2"

Optical Properties

Color:

Green

Wavelength (nm):

530

Working Distance (mm):

25

Hardware & Interface Connectivity

Connector:

Flying Leads

Power Supply:

Power Supply Required and Sold Separately.

USA: #66-855

Europe: **#66-855**

Japan: **#89-513**

Korea: **#33-773**

China: #66-855

Environmental & Durability Factors

Operating Temperature (°C):

0 to +60

Regulatory Compliance

Certificate of Conformance:

View

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited

Product Details

- Bright, Consistent Diffuse Illumination Over Field of View
- Unique Modular Heat Sink Design
- Internal Beamsplitter Ideal for Inspecting Highly Reflective Objects
- Excellent Light Stability

Advanced Illumination Diffuse Axial LED Illuminators are ideal for inspecting highly reflective optics. These coaxial illuminators provide even illumination over the field coverage. Advanced Illumination Diffuse Axial LED Illuminators feature vibration free performance and easily mount via M6 threaded holes.

Note: Required 24V power supply #66-855. **Accessories for Advanced Illumination products** are available and sold separately. Units cannot be intensity controlled.

Technical Information

