

Green M77 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-403 10 TO 12 DAYS



1



₹34,452.00

ADD TO CART

Qty 1-9
₹34,452.00
Qty 10+
₹32,729.00
Volume Pricing
Request Quote

Get Product Downloads
Blocking Wavelength Range (nm): 200-470, 600-950
Clear Aperture CA (mm): 73.00
Coating: Hard Coated
Filter Thread:

M77 x0.75
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 80.00
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 80.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View