

[See all 4 Products in Family](#)

Hemisphere Foot (Package of 4), Sorbothane Bumpers



Hemisphere Foot (Package of 4), Sorbothane Bumpers, #35-264

Stock **#35-264** **2 In Stock**

1 MRP ₹2,662

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-2	₹2,662 each
Qty 3+	₹2,372 each
Need More?	Request Quote

Product Downloads

General

Universal **Type:**

Physical & Mechanical Properties

1.0 **Thickness (inches):**

Sorbothane **Construction:**

2.00 **Diameter (inches):**

25-38 per bumper **Load Capacity (lbs):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.
