


[See all 5 Products in Family](#)

High Frequency, Premier Laser Diode Detector



Premier Laser Diode Detector



Stock #58-765 **3 In Stock**

MRP ₹13,806

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹13,806 each
Qty 10+	₹13,116 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

High Frequency **Type:**

Physical & Mechanical Properties

15.00	Diameter (mm):
54.50	Length (mm):
50.00	Weight (g):
Anodized Aluminum	Construction:

Optical Properties

20.00	Relative Ambient Light Rejection (dB):
-------	---

Electrical

>60	AC & DC S/N Ratio for 1mW Input (dB):
750.00	AC Output Frequency Response (kHz):
1.00	AC Output Sensitivity @ 650nm (V/mW):
<20	Current (mA):
5 - 10 DC	Voltage (V):

Hardware & Interface Connectivity

4 pin JST	Connector:
Power Supply Required and Sold Separately. USA: #59-099 Europe: Not Available Japan: #59-099 Korea: Not Available China: #59-099	Power Supply:

4 input/output leads	Electrical Leads/ Pin Connections:
----------------------	---

Environmental & Durability Factors

-40 to +85	Operating Temperature (°C):
90% RH	Operating Humidity:
-40 to +85	Storage Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
United Kingdom	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Designed for Use with the [Premier Laser Diodes](#)
- Wide Acceptance Angle
- Ideal for Particle Detection and Densitometry

Designed for use with the [Premier Laser Diodes](#), these detectors have a wide acceptance angle of 160 degrees and an amplification system, which makes them very versatile for indoor and outdoor applications. Condition monitoring such as fog and smoke, particle detection and densitometry are a few uses for the detector. The optional mount is a heavy duty clamp with a series of threaded holes for versatile integration at any angle. There is also a removable cover which exposes an M12 screw thread used for mounting.

A power supply, sold separately, is required for operation. We recommend [#59-099](#) 5V Universal Power Supply.