

# High Resolution Microscopy Star Target



High Resolution Mcroscopy Star Target, #37-538

Stock **#37-538** [CONTACT US](#)

⊖ 1 ⊕

₹135,198.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| ₹135,198.00                   |
| Qty 5+                        |
| ₹128,456.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Dimensions (mm):

10 x 10 x 1

Substrate:

[Fused Silica](#) w/Chrome deposit

Optical Density OD (Average):

OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm

|                                                                                   |
|-----------------------------------------------------------------------------------|
| <b>Construction:</b><br>Stainless Steel, 75 x 25 x 1.5mm, microscope slide format |
| <b>Pattern:</b><br>1 central Siemens star with 36 segment pairs, 8mm diameter     |
| <b>Spectral Range:</b><br>200 - 2000nm                                            |
| <b>Pattern Tolerance:</b><br>100nm/cm = 10 <sup>-5</sup>                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Reach 191:</b><br><a href="#">Compliant</a>             |
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |