

Hoya B390 (UV-VIS) 50mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-783** 10 TO 12 DAYS

[Additional Bandwidths](#)

- 1 +

₹9,396.00

ADD TO CART

Qty 1-10
₹9,396.00

Qty 11+
₹8,352.00

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Center Wavelength CWL (nm):

390.00
Density (g/cm³): 2.57
Full Width-Half Max FWHM (nm): 125.00
Glass/Filter Number: Hoya B390
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Blue-Violet
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View