

Hoya R64 (640nm), 50.8mm Sq., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-885 10 TO 12 DAYS

-

1

+

₹7,656.00

ADD TO CART

Qty 1-10
₹7,656.00

Qty 11+
₹6,786.00

Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Cut-On Wavelength (nm):
640.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya R64
Substrate: Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 60-40
Transformation Temperature (°C): 555
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View