

Hoya R70 (700nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-887 10 TO 12 DAYS

-

1

+

₹2,784.00

ADD TO CART

Qty 1-10

₹2,784.00

Qty 11+

₹2,436.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
700.00 ±10

Density (g/cm³):
2.86

Glass/Filter Number: Hoya R70
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Transformation Temperature (°C): 525
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed
Δλ (nm): <45
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View