

# Hoya U330 (UV) 50.8mm Square, 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-765** 10 TO 12 DAYS

- 1 +

**₹14,703.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| ₹14,703.00                    |
| Qty 11+                       |
| ₹12,963.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Dimensions (mm):  
50.80 x 50.80

Center Wavelength CWL (nm):  
330.00

|                                                                  |
|------------------------------------------------------------------|
| <div>Density (g/cm³):<br/>2.78</div>                             |
| <div>Full Width-Half Max FWHM (nm):<br/>140.00</div>             |
| <div>Glass/Filter Number:<br/><a href="#">Hoya U330</a></div>    |
| <div>Substrate: <input type="checkbox"/><br/>Colored Glass</div> |
| <div>Coating:<br/>Uncoated</div>                                 |
| <div>Color:<br/>Black</div>                                      |
| <div>Surface Quality:<br/>60-40</div>                            |
| <div>Thickness (mm):<br/>1.00</div>                              |
| <div>Thickness Tolerance (mm):<br/>±0.1</div>                    |
| <div>Type:<br/>Bandpass Filter</div>                             |
| <div>Wavelength:<br/>UV</div>                                    |
| <div>Parallelism (arcmin):<br/>≤2</div>                          |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                  |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |