


Hoya U340 (UV) 50mm Dia., 2.5mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-769** 10 TO 12 DAYS

[Additional Bandwidths](#)

-

1

+

₹14,703.00

ADD TO CART

Qty 1-10
₹14,703.00
Qty 11+
₹12,963.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Center Wavelength CWL (nm):

340.00
Density (g/cm³): 2.92
Full Width-Half Max FWHM (nm): 85.00
Glass/Filter Number: Hoya U340
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View