

# Hoya UV28N (280nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-796 10 TO 12 DAYS

-

1

+

₹7,656.00

ADD TO CART

|           |
|-----------|
| Qty 1-10  |
| ₹7,656.00 |

|           |
|-----------|
| Qty 11+   |
| ₹6,786.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
50.00

Cut-On Wavelength (nm):  
280.00 ±7

Density (g/cm³):  
2.61

|                                                             |
|-------------------------------------------------------------|
| <b>Glass/Filter Number:</b><br><a href="#">Hoya UV28N</a>   |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Color:</b><br>Clear                                      |
| <b>Surface Quality:</b><br>60-40                            |
| <b>Transformation Temperature (°C):</b><br>572              |
| <b>Thickness (mm):</b><br>2.50                              |
| <b>Thickness Tolerance (mm):</b><br>±0.1                    |
| <b>Type:</b><br>Longpass Filter                             |
| <b>Wavelength:</b><br>UV                                    |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                  |
| <b>Reflection Factor P<sub>d</sub>:</b><br>0.92             |
| <b>Bevel:</b><br>Protective as needed                       |
| <b>Δλ (nm):</b><br><45                                      |
| <b>TH (%):</b><br>>85                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |