

Hoya Y52 (520nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-872 10 TO 12 DAYS

-

1

+

₹2,784.00

ADD TO CART

Qty 1-10
₹2,784.00
Qty 11+
₹2,436.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
520.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya Y52
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View