

[See all 64 Products in Family](#)

# IDS GV-51J0FA-M-GL, GigE, 2/3" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock **#78-082** [CONTACT US](#)

MRP ₹1,26,909

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,26,909 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

**Spectrum:**  
Monochrome

## General

**Type:**  
Monochrome Camera

**Model Number:**  
GV-51J0FA-M-GL

IDS Imaging Development Systems **Manufacturer:**

uEye+ FA **Camera Series:**

## Physical & Mechanical Properties

41 x 53 x 42.7 (excludes connectors and lens mount) **Dimensions (mm):**

178 **Weight (g):**

Full **Housing:**

## Sensor

128MB **Image Buffer:**

2/3" **Sensor Format:**

8.13 **Resolution (Megapixels):**

15.00 **Frame Rate (fps):**

2,856 x 2,848 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V (µm):**

7.825 x 7.804 **Sensing Area, H x V (mm):**

Sony IMX546 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

0.009ms - 2000ms **Exposure Time:**

70.00 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

## Electrical

2 - 4 **Power Consumption (W):**

## Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE M12, screwable **Connector:**

Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#) **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Power Supply, 1 Ground **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Binder connector (Binder series 712: 09-0427-020-08) **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#19-694](#) **Mounting Threads:**

## Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

Storage Temperature (°C):  
-20 to +60

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 251:**

**Country of Origin:**  
Germany

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.