

IDS GV-5260FA-C-HQ, GigE, 1/1.2" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock #78-091 **1 In Stock**

MRP ₹98,766

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹98,766 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

GV-5260FA-C-HQ **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ FA **Camera Series:**

Physical & Mechanical Properties

41 x 53 x 42.7 (excludes connectors and lens mount) **Dimensions (mm):**

175 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1/1.2" **Sensor Format:**

2.30 **Resolution (Megapixels):**

46.00 **Frame Rate (fps):**

1,936 x 1,216 **Pixels (H x V):**

5.86 x 5.86 **Pixel Size, H x V (µm):**

11.345 x 7.126 **Sensing Area, H x V (mm):**

Sony IMX249 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

0.031ms - 2000ms **Exposure Time:**

74.00 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

Electrical

1.6 - 2.9 **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE M12, screwable **Connector:**

Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#) **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Power Supply, 1 Ground **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Binder connector (Binder series 712: 09-0427-020-08) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#19-694](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60

Storage Temperature (°C):

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 251:

Germany

Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.