

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [IDS Imaging uEye LE/XLE USB3.1 Cameras](#)

[See all 33 Products in Family](#)

IDS Imaging U3-3271LE-C-HQ 1/1.8" Color Board Level USB 3.1 Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE Camera (M12, Board Level, Front View)



Stock **#24-091** 10 TO 12 DAYS

[Similar Cameras](#)

⊖ 1 ⊕

₹55,245.00

ADD TO CART

Qty 1+
₹55,245.00
Volume Pricing
Request Quote

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
IDS Imaging

Mounting Threads: N/A
Image Buffer: Not Specified
Camera Family: uEye LE
Model Number: U3-3271LE-C-HQ Rev.1.2
Imaging Sensor: Sony IMX265
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 3.10
Pixels (H x V): 2,048 x 1,536
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 7.06 x 5.30
Frame Rate (fps): 58.00
Pixel Depth: 12 bit
Exposure Time: 25µs - 1.9s
Connector: USB Type-C
Power Supply: Power over USB
Power Consumption (W): 1 - 2
GPIOs: 2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground
Synchronization: Hardware Trigger (GPIO); Software Trigger
Dimensions (mm): 36 x 36 x 20 (excludes connectors and lens mount)
Weight (g): 16
Mount: M12 x 0.5 (S-Mount)
Housing: Board Level
Interface Port Orientation: Back Back (Right Angle)
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 10-pin Wuerth
Machine Vision Standard: USB3 Vision v1.1

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View