

[See all 63 Products in Family](#)

## IDS U3-3861LE-M-GL-VU, USB 3.0, 1/2.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #78-133 [CONTACT US](#)

1 MRP ₹48,852

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹48,852 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome

Spectrum:

### General

Monochrome Camera

Type:

U3-3861LE-M-GL-VU

Model Number:

**Manufacturer:**  
IDS Imaging Development Systems

**Camera Series:**  
uEye+ LE

## Physical & Mechanical Properties

**Dimensions (mm):**  
36 x 36 x 26 (excludes connectors and lens mount)

**Weight (g):**  
15

**Housing:**  
Board Level

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/2.8"

**Resolution (Megapixels):**  
2.12

**Frame Rate (fps):**  
135.00

**Pixels (H x V):**  
1,936 x 1,096

**Pixel Size, H x V (µm):**  
2.90 x 2.90

**Sensing Area, H x V (mm):**  
5.61 x 3.175

**Imaging Sensor:**  
Sony IMX290

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Rolling

**Pixel Depth:**  
12 bit

**Exposure Time:**  
0.011ms - 1649ms

**Dynamic Range (dB):**  
72.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
1 - 1.5

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB Type-C

**Power Supply:**  
Power over USB

**GPIO Connector Type:**  
10-pin Wuerth connector (WR-WTB 1.00 mm)

## Threading & Mounting

**Mount:**  
S-Mount (M12 x 0.5)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +80

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
Germany

**Imported By:**  
Edmund Optics India Private Limited

## Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

---

;