

TECHSPEC® IR (1150-1550nm) OD 4.0 25nm Bandpass Filter Kit, 12.5mm Dia



Stock #88-295 [CONTACT US](#)

-

1

+

₹107,010.00

ADD TO CART

Qty 1+
₹107,010.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
25.00

Filters Included :
CWL: [1150nm](#), [1200nm](#), [1250nm](#), [1300nm](#), [1350nm](#),
[1400nm](#), [1450nm](#), [1500nm](#), [1550nm](#)

Coating:
Hard Coated

Type: Bandpass Filter
Typical Applications: LED Cleanup, Bio-Imaging, Machine Vision
Wavelength: IR
Number of Filters: 9
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A 3.4.1.1 Abrasion: MIL-C-48497A 3.4.1.3 Temperature: MIL-C-48497A 3.4.2.1 Cleaning: MIL-C-48497A 3.4.2.11

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View