

IR Adjustable LED Ring Light



Stock #34-863 10 TO 12 DAYS

-

1

+

₹65,250.00

ADD TO CART

Qty 1+
₹65,250.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Infrared

Connector:
M12, 5 pins

Inner Diameter (mm):
58.0

Input Voltage (V):
24VDC

Mount: M4 (x4) and 3.5mm Thru (x4)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 151.0 x 117.0 x 40.0
Wavelength (nm): 850.00
Weight (g): 400.00
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Type of Illumination: LED Illuminator
Geometry: Ring Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP65

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View