

# IR M30.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-765 10 TO 12 DAYS

-

1

+

₹10,440.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹10,440.00                    |
| Qty 10+                       |
| ₹9,953.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Blocking Wavelength Range (nm):  
200-791

Clear Aperture CA (mm):  
25.50

Coating:  
Hard Coated

Filter Thread:

|                                                        |
|--------------------------------------------------------|
| M30.5 x 0.50                                           |
| <b>Color:</b><br>IR                                    |
| <b>Center Wavelength CWL (nm):</b><br>850.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>160.00        |
| <b>Mount Thickness (mm):</b><br>5.2                    |
| <b>Mount Thickness Including Threads (mm):</b><br>7.0  |
| <b>Outer Diameter (mm):</b><br>32.50                   |
| <b>Substrate Thickness (mm):</b><br>1.3                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |