

[See all 20 Products in Family](#)

## JAI Go-X, 8901C-PGE, 1" 8.9MP, GigE Color Camera



Stock #29-151 **1 In Stock**

- 1 + MRP ₹1,96,470

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,96,470 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Color **Spectrum:**

### General

Color Camera **Type:**

GOX-8901C-PGE **Model Number:**

JAI **Manufacturer:**

Go-X **Camera Series:**

## Physical & Mechanical Properties

29 x 29 x 51.5 **Dimensions (mm):**

65 **Weight (g):**

Full **Housing:**

## Sensor

1" **Sensor Format:**

8.90 **Resolution (Megapixels):**

12.00 **Frame Rate (fps):**

4,096 x 2,160 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

14.1 x 7.4 **Sensing Area, H x V (mm):**

Sony IMX267 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

GigE Vision **Machine Vision Standard:**

## Electrical

3.7 **Power Consumption (W):**

## Hardware & Interface Connectivity

GigE (PoE) **Interface:**

RJ45 with Screw Locks **Connector:**

**Power Supply:**  
Power Supply Required and Sold Separately:  
USA: #29-171  
Europe: #29-171  
Japan: #29-171  
Korea: Not Available  
China: Not Available

Hardware Trigger (GPIO) or Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

6-pin Hirose **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

-5 to +45 **Operating Temperature (°C):**

-25 to +60 **Storage Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI® Go-X Series Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.

---