

Laboratory Spectrometer



Stock #88-406 10 TO 12 DAYS

- 1 +

₹226,200.00

ADD TO CART

Qty 1+
₹226,200.00
Qty 2+
₹214,890.00
Volume Pricing
Request Quote

Get Product Downloads

Operating Temperature (°C):
5 to 35

Slit Width (µm):
50.00

Weight (kg):
0.34

Type of Sensor:
1024 pixels

Spectral Resolution (nm): <2.5
Spectrograph f/#: f/3.6
Software: BWSpec™
Wavelength Range (nm): 380 - 750
Dimensions (mm): 102 x 67 x 34
Integration Time: 1 - 65,535 ms
Computer Interface: USB 2.0
Operating System: Windows® 7, 8, 8.1, 10 (32-bit and 64-bit)
Digitizer: 16-bit or 65,535:1
Power Requirement: Powered by USB 5 V < 0.5 A
Wavelength Accuracy Tolerance (nm): ≤0.7 @ 546.7nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
