

Large X-Axis Leadscrew Drive



X-Y Axis Leadscrew Drive Metric Stages



Stock **#36-032** **20+ In Stock**

-

1

+

₹17,824

ADD TO CART

Volume Pricing	
Qty 1-9	₹17,824 each
Qty 10+	₹15,741 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
	Guide System:

Dovetail	
40 x60	Stage Size (mm):
15 (±7.5)	Travel (mm):
M16 x1	Center Hole:
Brass	Construction:
0.5	Leadscrew Pitch (mm):
7.5	Load Capacity (kg):
0.38	Weight (kg):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

(1) M16 x 1, (4) M4 x0.7, (6) M3 x0.5	Mounting Threads:
---------------------------------------	-------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Locking Knobs for Secure Positioning
- 0.5mm Travel per Knob Rotation
- Available with up to 15mm Travel in Xand Y with 12mm Travel in Z

Leadscrew Drive Stages are ideal for a variety of positioning requirements that require high load capacities. Each stage features a leadscrew drive and locking knobs for securing the stage position. A top plate is available for large models ([#58-290](#)) with both M6 and ¼-20 tapped holes to directly accept posts or post holders. Large models feature an aluminum base plate for easy integration.

Technical Information

