

# Laser USB 450nm 50mW



Stock #26-935 2 In Stock

-

1

+

₹46,800

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹46,800 each                  |
| Qty 10+        | ₹41,940 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                        |
|----------------------------------|------------------------|
| IIIB                             | Laser Class - CDRH:    |
| Physical & Mechanical Properties |                        |
| 19                               | Housing Diameter (mm): |
| 90.00                            | Length (mm):           |
| Optical Properties               |                        |

|            |                            |
|------------|----------------------------|
| 450.00     | Wavelength (nm):           |
| ±5         | Wavelength Tolerance (nm): |
| 4.5        | Beam Diameter (mm):        |
| Adjustable | Beam Divergence (mrad):    |
| Indigo     | Color:                     |

Electrical

|          |                             |
|----------|-----------------------------|
| 50       | Output Power (mW):          |
| 0.1 - 50 | Modulation Frequency (kHz): |

Hardware & Interface Connectivity

|                |                        |
|----------------|------------------------|
| 5              | Operating Voltage (V): |
| USB 5V±0.5V 1A | Power Supply:          |

Environmental & Durability Factors

|         |                             |
|---------|-----------------------------|
| 10 - 35 | Operating Temperature (°C): |
|---------|-----------------------------|

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 233:                  |
| China                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

Product Details

- USB Powered and Controllable via Computer
- Software Allows for Modulation and Output Power Control
- Available in Wavelengths From 405nm to 940nm

USB Powered Alignment Laser Diode Modules can be easily connected, configured, and powered by common USB hardware. No external power supply is required, and when disconnected from the computer, these lasers will retain their settings (such as modulation and output power) allowing for flexibility in system design and layout. These lasers can also be plugged into a 5V USB power adapter for simple on/off functionality when more detailed control is unnecessary. USB Powered Alignment Laser Diode Modules' software provides simple user adjustment of output power and modulation of the laser beam. A variety of laser diode wavelengths are available, ranging from VIS to IR. These laser diodes are ideal for space constrained alignment applications.