

Laser ZX20 405nm 160mW, 20°



Stock #19-425 10 TO 12 DAYS

- 1 +

₹153,990.00

ADD TO CART

Qty 1-9
₹153,990.00
Qty 10+
₹138,591.00
Volume Pricing
Request Quote

Get Product Downloads



Operating Temperature (°C):
-10 to +50

Output Power (mW):
160

Power Stability (%):
±3

Wavelength (nm):
405.00

Weight (g): 90
Laser Class - IEC: 3B
Housing Length (mm): 97
Housing Diameter (mm): 20
Storage Temperature (°C): -40 to +85
Bore Sighting (mrad): <0.8
Pointing Stability (µrad/°C): <10
Modulation Frequency (kHz): 400
Style: Homogeneous Line
Manufacturer: Z-Laser
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Violet
Connector: 5 pins, M12
Fan Angle (°): 20.00
Focus Range: 100mm to Collimation
Input Voltage (V): 9 - 30 DC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View