

Light Red M39 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-423 10 TO 12 DAYS

-

1

+

₹13,311.00

ADD TO CART

Qty 1-9
₹13,311.00
Qty 10+
₹12,685.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-570, 700-1101

Clear Aperture CA (mm):
34.00

Coating:
Hard Coated

Filter Thread:

M39 x 0.50
Color: Light Red
Center Wavelength CWL (nm): 635.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 60.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 41.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View