

[See all 9 Products in Family](#)

M12 Female to Male, 5 pin, 0.2m

See More by [Advanced Illumination](#)



#33-462: M12 Female to Male, 5 pin, 0.2m

Stock **#33-462** **1 In Stock**

⊖ 1 ⊕ ₹3,600

ADD TO CART

Volume Pricing	
Qty 1+	₹3,600 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Advanced Illumination **Manufacturer:**

Regulatory Compliance

Compliant **RoHS 2015:**

Certificate of Conformance:

[View](#)

Compliant **Reach 233:**

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited

Product Details

- DaisyChain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Backlight illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Backlight illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator's customizability.

Note: A 24V power supply is required.

Technical Information

Typical Intensity		
Size	50 x 75mm	100 x 150mm
Working Distance	At Surface	At Surface
Area	58 x 38mm	124 x 91mm
Typical Irradiance (W/M ²)	101	140
Typical Illuminance (kLux)	38	52